

MICRO alésoirs

Micro alésoirs

Mikro-Reibahlen

Micro reamers

Micro alesatori

2

5

0

0

4

4

1

0


MD
HM/SC
MG

Alésoirs
Reibahlen
Reamers
Alesatori




D
<
d

Z4
↓



$\lambda -10^\circ$

250.044.10



OPTI
cut

nouveau

Livable de stock tous
les 5 microns

Norme OPTI

$D_{+/-0.001}$	d_{h6}	l_1	l_2	L	Z	Non revêtu
0.6 - 0.695	3	7	14	50	4	250.044.10-...
0.7 - 0.795	3	7	14	50	4	250.044.10-...
0.8 - 0.82	3	7	14	50	4	250.044.10-...
0.825 - 0.895	3	8	16	50	4	250.044.10-...
0.9 - 0.995	3	8	16	50	4	250.044.10-...
1 - 1.095	3	8	16	50	4	250.044.10-...
1.1 - 1.12	3	8	16	50	4	250.044.10-...
1.125 - 1.195	3	10	18	50	4	250.044.10-...
1.2 - 1.295	3	10	18	50	4	250.044.10-...
1.3 - 1.395	3	10	18	50	4	250.044.10-...
1.4 - 1.43	3	10	18	50	4	250.044.10-...
1.435 - 1.495	3	10	20	50	4	250.044.10-...
1.5 - 1.595	3	10	20	50	4	250.044.10-...
1.6 - 1.695	3	10	20	50	4	250.044.10-...
1.7 - 1.73	3	10	20	50	4	250.044.10-...
1.735 - 1.795	3	10	22	50	4	250.044.10-...
1.8 - 1.895	3	10	22	50	4	250.044.10-...
1.9 - 1.995	3	10	22	50	4	250.044.10-...
2 - 2.03	3	10	22	50	4	250.044.10-...